

# US38-P Cut Sheet



HydroMode potable water push-to-connect fitting, union straight, acetal body, (2) 3/8in tube connection(s), NSF/ANSI 61. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/US38-P>

## Technical Specifications

<b>Brand</b>	HydroMode
<b>Item</b>	Potable water Push-to-connect Fitting
<b>Fitting Type</b>	Union straight
<b>Body Material</b>	Acetal
<b>Port Connection Info</b>	(2) 3/8in tube
<b>Operating Pressure</b>	145 psi
<b>Operating Temperature</b>	32 to 158 deg F
<b>Agency Approval</b>	NSF/ANSI 61
<b>Quantity per Pack</b>	5

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>