

UT12M Cut Sheet



NITRA pneumatic push-to-connect fitting, union tee, thermoplastic (PBT) body, (3) 12mm push-to-connect connection(s). Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UT12M>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Type	Union tee
Body Material	Thermoplastic (PBT)
Thread Sealant	No
Fitting Measurement Type	Metric
Connection	(3) 12mm push-to-connect
Operating Pressure	-29.5in Hg to 150 psi
Operating Temperature	32 to 140 deg F
Quantity per Pack	5
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/UT12M.pdf>
See store item page for other formats.