

UT16M Cut Sheet



NITRA pneumatic push-to-connect fitting, union tee, thermoplastic (PBT) body, (3) 16mm push-to-connect connection(s). Package of 3.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UT16M>

Technical Specifications

| | |
|--------------------------|---------------------------|
| Brand | NITRA |
| Item | Fitting |
| Working Fluid | Air or inert gas |
| Fitting Connection Type | Push-to-connect |
| Fitting Type | Union tee |
| Body Material | Thermoplastic (PBT) |
| Thread Sealant | No |
| Fitting Measurement Type | Metric |
| Connection | (3) 16mm push-to-connect |
| Operating Pressure | -29.5in Hg to 150 psi |
| Operating Temperature | 32 to 140 deg F |
| Quantity per Pack | 3 |
| For Use With | Flexible pneumatic tubing |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/UT16M.pdf>
See store item page for other formats.