

UTR12-38 Cut Sheet



NITRA pneumatic push-to-connect fitting, union tee reducer, thermoplastic (PBT) body, (2) 1/2in tube to 3/8in tube connection(s). Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UTR12-38>

Technical Specifications

| | |
|------------------------------|---|
| Brand | NITRA |
| Item | Pneumatic Push-to-connect Fitting |
| Fitting Type | Union tee reducer |
| Body Material | Thermoplastic (PBT) |
| Thread Sealant | No |
| Connection | (2) 1/2in push-to-connect and 3/8in push-to-connect |
| Operating Pressure | -29.5in Hg to 150 psi |
| Operating Temperature | 32 to 140 deg F |
| Quantity per Pack | 5 |
| For Use With | Flexible pneumatic tubing |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |