

# UTR38-516 Cut Sheet



NITRA pneumatic push-to-connect fitting, union tee reducer, thermoplastic (PBT) body, (2) 3/8in push-to-connect to (1) 5/16in (8mm) push-to-connect. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UTR38-516>

## Technical Specifications

|                          |  |
|--------------------------|--|
| Brand                    | NITRA  |
| Item                     | Fitting  |
| Working Fluid            | Air or inert gas   |
| Fitting Connection Type  | Push-to-connect  |
| Fitting Type             | Union tee reducer  |
| Body Material            | Thermoplastic (PBT)  |
| Thread Sealant           | No   |
| Fitting Measurement Type | Metric and SAE   |
| Connection               | (2) 3/8in push-to-connect and (1) 5/16in (8mm) push-to-connect |
| Operating Pressure       | -29.5in Hg to 150 psi  |
| Operating Temperature    | 32 to 140 deg F  |
| Quantity per Pack        | 5  |
| For Use With             | Flexible pneumatic tubing                                      |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/UTR38-516.pdf>  
See store item page for other formats.