

# UV14GRN100 Cut Sheet



NITRA pneumatic tubing, ether-based polyurethane, dark green, 1/4in outside diameter, 0.156in inside diameter, UV stabilized, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UV14GRN100>

## Technical Specifications

|                       |                          |
|-----------------------|--------------------------|
| Brand                 | NITRA                    |
| Item                  | Tubing                   |
| Working Fluid         | Air or inert gas         |
| Material              | Ether-based polyurethane |
| Color                 | Dark green               |
| Outside Diameter      | 1/4in                    |
| Inside Diameter       | 0.156in                  |
| UV stabilized         | Yes                      |
| Working Length        | 100ft package            |
| Operating Pressure    | 180 psi                  |
| Operating Temperature | -40 to +160 deg F        |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |