

# UX12M Cut Sheet



NITRA pneumatic push-to-connect fitting, union cross, thermoplastic (PBT) body, (4) 12mm tube connection(s). Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UX12M>

## Technical Specifications

|                              |                                   |
|------------------------------|-----------------------------------|
| <b>Brand</b>                 | NITRA                             |
| <b>Item</b>                  | Pneumatic Push-to-connect Fitting |
| <b>Fitting Type</b>          | Union cross                       |
| <b>Body Material</b>         | Thermoplastic (PBT)               |
| <b>Thread Sealant</b>        | No                                |
| <b>Connection</b>            | (4) 12mm push-to-connect          |
| <b>Operating Pressure</b>    | -29.5in Hg to 150 psi             |
| <b>Operating Temperature</b> | 32 to 140 deg F                   |
| <b>Quantity per Pack</b>     | 5                                 |
| <b>For Use With</b>          | Flexible pneumatic tubing         |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |