

# UY12-P Cut Sheet



HydroMode potable water push-to-connect fitting, union Y, acetal body, (3) 1/2in tube connection(s), NSF/ANSI 61. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/UY12-P>

## Technical Specifications

|                              |                           |
|------------------------------|---------------------------|
| Brand                        | HydroMode                 |
| Item                         | Fitting                   |
| Working Fluid                | Potable water             |
| Fitting Connection Type      | Push-to-connect           |
| Fitting Type                 | Union Y                   |
| Body Material                | Acetal                    |
| Connection                   | (3) 1/2in push-to-connect |
| Operating Pressure           | 145 psi                   |
| Operating Temperature        | 32 to 158 deg F           |
| Potable Water Certifications | NSF/ANSI 61               |
| Quantity per Pack            | 5                         |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/UY12-P.pdf>  
See store item page for other formats.