


V40174-1 Cut Sheet



Southwire flexible control cable, unshielded, 9 conductors (includes ground), 18 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/V40174-1>

Technical Specifications

Brand	Southwire	Shielding	Unshielded
Item	Cable	Jacket Material	TPE
Wire/Cable Type	Control	Jacket Color	Gray
UL Wire/Cable Type	TC, TC-ER, WTTTC and MTW	Nominal Overall Cable Diameter	0.39in
Application	General purpose	Bulk Length	Cut to length
Flexibility	Flexible	Package Type	1 to 50ft = Coil, 51 to 250ft = 14 x 7in Reel, 251 to 360ft = 14 x 10in Reel, 361 to 560ft = 16 x 10in Reel, 561 to 800ft = 18 x 10in Reel, 801 to 1040ft = 18 x 13in Reel, 1041 to 2240ft = 24 x 17in Wooden Reel, 2241 to 3680ft = 30 x 17in Wooden Reel, 3681 to MAX = Large Wooden Reel
Voltage Rating	600V (Types TC, TC-ER, MTW), 1000V (Type WTTTC)		
Conductors	9 conductors (includes ground)		
Conductor Size	18 AWG		
Conductor Stranding	16-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	PVC/Nylon		
Conductor Insulation Color	Black with white numbers and green/yellow ground		

Agency Approvals

UL Listed File #	E75755
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement