


V40178-1 Cut Sheet



Southwire flexible control cable, unshielded, 18 conductors (includes ground), 18 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, TPE jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/V40178-1>

Technical Specifications

Brand	Southwire	Shielding	Unshielded
Item	Cable	Jacket Material	TPE
Wire/Cable Type	Control	Jacket Color	Gray
UL Wire/Cable Type	TC, TC-ER, WTTC and MTW	Nominal Overall Cable Diameter	0.55in
Applicable Standards	ECOLAB	Bulk Length	Cut to length
Application	General purpose	Package Type	• 20 to 50ft = Coil
Flexibility	Flexible		• 51 to 130ft = 14 x 7in Reel
Voltage Rating	600V (Types TC, TC-ER, MTW), 1000V (Type WTTC)		• 131 to 185ft = 14 x 10in Reel
Conductors	18 conductors (includes ground)		• 186 to 280ft = 16 x 10in Reel
Conductor Size	18 AWG		• 281 to 395ft = 18 x 10in Reel
Conductor Stranding	16-stranded		• 396 to 515ft = 18 x 13in Reel
Conductor Material	Bare copper		• 516 to 1150ft = 24 x 17in Wooden Reel
Conductor Insulation Material	PVC/Nylon		• 1151 to 1835ft = 30 x 17in Wooden Reel
Conductor Insulation Color	Black with white numbers and green/yellow ground		• 1836 to 5000ft = Large Wooden Reel

Agency Approvals

UL Listed File #	E75755
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement