

# VADT150-42-24 Cut Sheet



AcuAMP AC/DC voltage transducer, 0-150 VAC/VDC sensing range, True RMS, 4-20 mA output.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VADT150-42-24>

## Technical Specifications

|                       |                    |
|-----------------------|--------------------|
| Brand                 | AcuAMP             |
| Item                  | Voltage transducer |
| Voltage Type          | AC/DC              |
| Sensing Range         | 0-150 VAC/VDC      |
| True RMS              | Yes                |
| Output                | 4-20 mA            |
| Operating Voltage     | 24 VAC/VDC         |
| Mounting              | 35mm DIN rail      |
| Electrical Connection | Screw terminals    |
| UL Rating             | UL 508 listed      |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E222847                                |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/VADT150-42-24.pdf>  
See store item page for other formats.