

VBC25R38T-25 Cut Sheet



Minerallac vertical flange rod hanger, package of 25. For use with 1/16 to 1/4in vertical flange and 3/8-18 UNC threaded rod.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VBC25R38T-25>

Technical Specifications

Brand	Minerallac
Item	Rod hanger
Hanger Type	Vertical flange
Load Rating	160 lbs
Material	Steel
Finish	Zinc plated
Minimum Flange Thickness	1/16in
Maximum Flange Thickness	1/4in
Quantity per Pack	25
For Use With	1/16 to 1/4in vertical flange and 3/8-18 UNC threaded rod

Agency Approvals

CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document