

# VBC25R38T Cut Sheet



Minerallac vertical flange rod hanger, package of 100. For use with 1/16 to 1/4in vertical flange and 3/8-18 UNC threaded rod.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VBC25R38T>

## Technical Specifications

|                          |  |
|--------------------------|--|
| Brand                    | Minerallac   |
| Item                     | Rod hanger   |
| Hanger Type              | Vertical flange  |
| Load Rating              | 160 lbs  |
| Material                 | Steel  |
| Finish                   | Zinc plated  |
| Minimum Flange Thickness | 1/16in   |
| Maximum Flange Thickness | 1/4in  |
| Quantity per Pack        | 100  |
| For Use With             | 1/16 to 1/4in vertical flange<br>and 3/8-18 UNC threaded rod |

## Agency Approvals

|             |  |
|-------------|--|
| CE          | None                                   |
| CSA File #  | None                                   |
| RoHS Status | No                                     |
| EU REACH    | <a href="#">View EU REACH document</a> |