

VCST-25-1000 Cut Sheet



ProSense vibration switch/transmitter, 0 to 25 mm/s RMS, 10-1000 Hz, switch or current output, M8 x 1.25 male threads process connection, 4-pin M12 quick-disconnect, 18-32 VDC operating voltage, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VCST-25-1000>

Technical Specifications

Brand	ProSense
Item	Vibration switch/transmitter
Measuring Range	0 to 25 mm/s RMS
Frequency Range	10-1000 Hz
Output	Switch (N.C.), PNP
Output 2	4-20 mA
Process Connection	M8 x 1.25 male threads
Electrical Connection	4-pin M12 quick-disconnect
Operating Temperature	-25 to 80 deg C
Operating Voltage	18-32 VDC
IP Rating	IP67
Additional Information	Purchased cable separately

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VCST-25-1000.pdf>
See store item page for other formats.