

VCT-25-1000 Cut Sheet



ProSense vibration transmitter, 0 to 25 mm/s RMS, 10-1000 Hz, 4-20 mA output, 1/4-28 UNF female process connection, 4-pin M12 quick-disconnect, 9.6-32 VDC operating voltage, IP67 IP68 IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VCT-25-1000>

Technical Specifications

Brand	ProSense
Item	Vibration transmitter
Measuring Range	0 to 25 mm/s RMS
Frequency Range	10-1000 Hz
Output	4-20 mA
Process Connection	1/4-28 UNF female
Electrical Connection	4-pin M12 quick-disconnect
Operating Temperature	-30 to 125 deg C
Operating Voltage	9.6-32 VDC
IP Rating	IP67 IP68 IP69K
Includes	(1) 1/4-28 UNF male to M8 x 1.25mm male process adapter and (1) 1/4-28 UNF male to 1/4-28 UNF male process adapter
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VCT-25-1000.pdf>
See store item page for other formats.