VCTP-0.5-1000 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



ProSense vibration transmitter, 0–0.5 in/s peak, 1 axis, 10–1000 Hz, current output, 1/4-28 UNF female process connection, 4-pin M12 quick-disconnect, 12–30 VDC operating voltage, IP67 and IP68.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/VCTP-0.5-1000

Technical Specifications

Brand	ProSense
Item	Vibration transmitter
Measuring Range	0–0.5 in/s peak
Number of Axes	1
Frequency Range	10–1000 Hz
Output	4–20 mA
Process Connection	1/4-28 UNF female
Electrical Connection	4-pin M12 quick-disconnect

Operating Temperature	-40 to +105 °C
Operating Voltage	12–30 VDC
IP Rating	IP67 and IP68
Includes	(1) 1/4-28 UNF male to M8 x 1.25mm male process adapter and (1) 1/4-28 UNF male to 1/4-28 UNF male process adapter
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/VCTP-0.5-1000.pdf
See store item page for other formats.