

VDCT050-42-24 Cut Sheet



AcuAMP DC voltage transducer, 0-50 VDC sensing range, 4-20 mA output.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VDCT050-42-24>

Technical Specifications

Brand	AcuAMP
Item	Voltage transducer
Voltage Type	DC
Sensing Range	0-50 VDC
True RMS	No
Output	4-20 mA
Operating Voltage	24 VAC/VDC
Mounting	35mm DIN rail
Electrical Connection	Screw terminals
UL Rating	UL 508 listed

Agency Approvals

UL Listed File #	E222847
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/VDCT050-42-24.pdf>
See store item page for other formats.