

VE0221S01 Cut Sheet

CCEA VEGA series LED light bar, 346mm length, 24 VDC operating voltage, daylight white, 5000K, 13W, recessed mount, pigtail, anodized aluminum body, 9.8ft/3m cable length, IP67 and IP69.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VE0221S01>

Technical Specifications

Brand	CCEA
Item	LED light bar
Series	VEGA
Length	346mm
Operating Voltage	24 VDC
LED Color	Daylight white
Color Temperature	5000K
Mounting	Recessed
Connection	Pigtail
Power Consumption	13W
Body Material	Anodized aluminum
Cable Length	9.8ft/3m
IP Rating	IP67 and IP69

Agency Approvals

UL Listed File #	None
UL Recognized File #	E506617
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VE0221S01.pdf>
See store item page for other formats.