

VE0321S02 Cut Sheet

CCEA VEGA series LED light bar, 466mm length, 24 VDC operating voltage, daylight white, 5000K, 19.5W, recessed mount, 4-pin M12 quick-disconnect, anodized aluminum body, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VE0321S02>

Technical Specifications

Brand	CCEA
Item	LED light bar
Series	VEGA
Length	466mm
Operating Voltage	24 VDC
LED Color	Daylight white
Color Temperature	5000K
Mounting	Recessed
Connection	4-pin M12 quick-disconnect
Power Consumption	19.5W
Body Material	Anodized aluminum
IP Rating	IP67
Requires	4-pin female M12 cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	E506617
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VE0321S02.pdf>
See store item page for other formats.