

VE0521S02 Cut Sheet

CCEA VEGA series LED light bar, 706mm length, 24 VDC operating voltage, daylight white, 5000K, 32.5W, recessed mount, 4-pin M12 quick-disconnect, anodized aluminum body, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VE0521S02>

Technical Specifications

| | |
|--------------------------|----------------------------|
| Brand | CCEA |
| Item | LED light bar |
| Series | VEGA |
| Length | 706mm |
| Operating Voltage | 24 VDC |
| LED Color | Daylight white |
| Color Temperature | 5000K |
| Mounting | Recessed |
| Connection | 4-pin M12 quick-disconnect |
| Power Consumption | 32.5W |
| Body Material | Anodized aluminum |
| IP Rating | IP67 |
| Requires | 4-pin female M12 cable |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | E506617 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VE0521S02.pdf>
See store item page for other formats.