

VFL75-100S-2D Cut Sheet



ProSense vibration fork liquid level switch, any orientation mount, 1.89in insertion length, 316L stainless steel wetted parts, -40 to 212 deg F, 3/4in male NPT process connection, AC/DC, 2-wire, N.O. or N.C., EN 175301-803-A connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFL75-100S-2D>

Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Vibration fork
Media Type	Liquid
Mounting	Any orientation
Insertion Length	1.89in
Process Connection	3/4in male NPT
Process Temperature	-40 to 212 deg F
Output	AC/DC, 2-wire, N.O. or N.C.
Operating Voltage	20-253 VAC/DC
Wetted Parts	316L stainless steel
Electrical Connection	EN 175301-803-A connector

Agency Approvals

CE	View CE declarations
CSA File #	600062
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/VFL75-100S-2D.pdf>
See store item page for other formats.