

# VFL75-100S-3D Cut Sheet



ProSense vibration fork liquid level switch, any orientation mount, 1.89in insertion length, 316L stainless steel wetted parts, -40 to 212 deg F, 3/4in male NPT process connection, switch PNP, 3-wire, N.O. or N.C., EN 175301-803-A connector.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFL75-100S-3D>

## Technical Specifications

Brand	ProSense
Item	Level switch
Sensor Type	Vibration fork
Media Type	Liquid
Mounting	Any orientation
Insertion Length	1.89in
Process Connection	3/4in male NPT
Process Temperature	-40 to 212 deg F
Output	Switch PNP, 3-wire, N.O. or N.C.
Operating Voltage	10-30 VDC
Wetted Parts	316L stainless steel
Electrical Connection	EN 175301-803-A connector

## Agency Approvals

CE	<a href="#">View CE declarations</a>
CSA File #	600062
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/VFL75-100S-3D.pdf>  
See store item page for other formats.