

# VFL75-100S-3H Cut Sheet



ProSense vibration fork liquid level switch, any orientation mount, 1.89in insertion length, 316L stainless steel wetted parts, -40 to 212 deg F, 3/4in male NPT process connection, switch PNP, 3-wire, N.O./N.C. complementary, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VFL75-100S-3H>

## Technical Specifications

|                              |                                             |
|------------------------------|---------------------------------------------|
| <b>Brand</b>                 | ProSense                                    |
| <b>Item</b>                  | Level switch                                |
| <b>Sensor Type</b>           | Vibration fork                              |
| <b>Media Type</b>            | Liquid                                      |
| <b>Mounting</b>              | Any orientation                             |
| <b>Insertion Length</b>      | 1.89in                                      |
| <b>Process Connection</b>    | 3/4in male NPT                              |
| <b>Process Temperature</b>   | -40 to 212 deg F                            |
| <b>Output</b>                | Switch PNP, 3-wire, N.O./N.C. complementary |
| <b>Operating Voltage</b>     | 10-30 VDC                                   |
| <b>Wetted Parts</b>          | 316L stainless steel                        |
| <b>Electrical Connection</b> | 4-pin M12 quick-disconnect                  |

## Agency Approvals

|                    |                                        |
|--------------------|----------------------------------------|
| <b>CE</b>          | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>  | 600062                                 |
| <b>RoHS Status</b> | Yes (See CE Doc)                       |
| <b>EU REACH</b>    | <a href="#">View EU REACH document</a> |