

VKHM-Z-VSM-Z-P4 Cut Sheet

di-soric patch cable signal converter, 4-pin M12 axial female to 4-pin M12 axial male, antivalence, 10–35 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VKHM-Z-VSM-Z-P4>

Technical Specifications

Brand	di-soric
Item	Signal converter
Form Factor	Patch cable
Connector Type	4-pin M12 axial female to 4-pin M12 axial male
Function	Antivalence
Operating Voltage	10–35 VDC
Operating Temperature	-20 to +70 °C
Material	Plastic
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/VKHM-Z_VSM-Z_P4.pdf
See store item page for other formats.