

VMR-1C-A-240A Cut Sheet



ProSense voltage monitor relay, 1-phase, socket mount, finger-safe, 180-300 VAC input voltage, SPDT, 10A contact rating, 8-pin, LED indicator(s), overvoltage, undervoltage and adjustable drop-out protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VMR-1C-A-240A>

Technical Specifications

Brand	ProSense
Item	Relay
Relay Type	Voltage monitor
Number of Phases	1
Mounting	Socket
Relay Housing Type	Finger-safe
Input Voltage	180-300 VAC
Relay Configuration	SPDT
Connector Type	8-pin
Contact Rating	10A
Indicator	LED
Protection Type(s)	<ul style="list-style-type: none">• overvoltage• undervoltage• adjustable drop-out
Additional Information	Relay becomes UL listed when used with Macromatic 70169-D relay socket

Agency Approvals

UL Listed File #	E191059
UL Recognized File #	E191059
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document