

VMR-2C-A-110D Cut Sheet



ProSense voltage monitor relay, 1-phase, socket mount, 83-138 VDC input voltage, DPDT, 10A contact rating, 8-pin, LED indicator(s), overvoltage, undervoltage and adjustable drop-out protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VMR-2C-A-110D>

Technical Specifications

| | |
|----------------------------|-----------------|
| Brand | ProSense |
| Item | Relay |
| Relay Type | Voltage monitor |
| Number of Phases | 1 |
| Mounting | Socket |
| Relay Housing Type | Finger-safe |
| Input Voltage | 83-138 VDC |
| Relay Configuration | DPDT |

| | |
|-------------------------------|--|
| Connector Type | 8-pin |
| Contact Rating | 10A |
| Indicator | LED |
| Protection Type(s) | <ul style="list-style-type: none">• overvoltage• undervoltage• adjustable drop-out |
| Additional Information | Relay becomes UL listed when used with Macromatic 70169-D relay socket |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E191059 |
| UL Recognized File # | E191059 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VMR-2C-A-110D.pdf>
See store item page for other formats.