

# VMR-2C-A-120A Cut Sheet



ProSense voltage monitor relay, 1-phase, socket mount, finger-safe, 90-150 VAC input voltage, DPDT, 10A contact rating, 8-pin, LED indicator(s), overvoltage, undervoltage and adjustable drop-out protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VMR-2C-A-120A>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Relay
<b>Relay Type</b>	Voltage monitor
<b>Number of Phases</b>	1
<b>Mounting</b>	Socket
<b>Relay Housing Type</b>	Finger-safe
<b>Input Voltage</b>	90-150 VAC
<b>Relay Configuration</b>	DPDT
<b>Connector Type</b>	8-pin
<b>Contact Rating</b>	10A
<b>Indicator</b>	LED
<b>Protection Type(s)</b>	<ul style="list-style-type: none"><li>• overvoltage</li><li>• undervoltage</li><li>• adjustable drop-out</li></ul>
<b>Additional Information</b>	Relay becomes UL listed when used with Macromatic 70169-D relay socket

## Agency Approvals

<b>UL Listed File #</b>	E191059
<b>UL Recognized File #</b>	E191059
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>