

VMR-2C-A-120A Cut Sheet



ProSense voltage monitor relay, 1-phase, socket mount, 90-150 VAC input voltage, DPDT, 10A contact rating, 8-pin, LED indicator(s), overvoltage, undervoltage and adjustable drop-out protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VMR-2C-A-120A>

Technical Specifications

| | | | |
|---------------------|-----------------|------------------------|--|
| Brand | ProSense | Connector Type | 8-pin |
| Item | Relay | Contact Rating | 10A |
| Relay Type | Voltage monitor | Indicator | LED |
| Number of Phases | 1 | Protection Type(s) | <ul style="list-style-type: none">• overvoltage• undervoltage• adjustable drop-out |
| Mounting | Socket | Additional Information | Relay becomes UL listed when used with Macromatic 70169-D relay socket |
| Relay Housing Type | Finger-safe | | |
| Input Voltage | 90-150 VAC | | |
| Relay Configuration | DPDT | | |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E191059 |
| UL Recognized File # | E191059 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VMR-2C-A-120A.pdf>
See store item page for other formats.