

VMR-2C-A-24D Cut Sheet



ProSense voltage monitor relay, 1-phase, socket mount, 18-30 VDC input voltage, DPDT, 10A contact rating, 8-pin, LED indicator(s), overvoltage, undervoltage and adjustable drop-out protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VMR-2C-A-24D>

Technical Specifications

Brand	ProSense	Connector Type	8-pin
Item	Relay	Contact Rating	10A
Relay Type	Voltage monitor	Indicator	LED
Number of Phases	1	Protection Type(s)	<ul style="list-style-type: none">• overvoltage• undervoltage• adjustable drop-out
Mounting	Socket	Additional Information	Relay becomes UL listed when used with Macromatic 70169-D relay socket
Relay Housing Type	Finger-safe		
Input Voltage	18-30 VDC		
Relay Configuration	DPDT		

Agency Approvals

UL Listed File #	E191059
UL Recognized File #	E191059
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VMR-2C-A-24D.pdf>
See store item page for other formats.