

# VMR-2C-F-120A Cut Sheet



ProSense voltage monitor relay, 1-phase, socket mount, 90-150 VAC input voltage, DPDT, 10A contact rating, 8-pin, LED indicator(s), overvoltage, undervoltage and fixed drop-out protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VMR-2C-F-120A>

## Technical Specifications

|                     |                 |                        |   |
|---------------------|-----------------|------------------------|---|
| Brand               | ProSense        | Connector Type         | 8-pin   |
| Item                | Relay           | Contact Rating         | 10A   |
| Relay Type          | Voltage monitor | Indicator              | LED   |
| Number of Phases    | 1               | Protection Type(s)     | <ul style="list-style-type: none"><li>• overvoltage</li><li>• undervoltage</li><li>• fixed drop-out</li></ul> |
| Mounting            | Socket          | Additional Information | Relay becomes UL listed when used with Macromatic 70169-D relay socket  |
| Relay Housing Type  | Finger-safe     |                        |   |
| Input Voltage       | 90-150 VAC      |                        |   |
| Relay Configuration | DPDT            |                        |   |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E191059                                |
| UL Recognized File # | E191059                                |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/VMR-2C-F-120A.pdf>  
See store item page for other formats.