

VRTP-100-A38 Cut Sheet



Elesa handwheel, spoked, 4in diameter, 3/8in bore, polypropylene, matte black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VRTP-100-A38>

Technical Specifications

| | |
|-------------------------|---------------|
| Brand | Elesa |
| Item | Handwheel |
| Wheel Type | Spoked |
| Nominal Diameter | 4in |
| Bore Diameter | 3/8in |
| Material | Polypropylene |
| Color | Matte black |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VRTP-100-A38.pdf>
See store item page for other formats.