

# VTF-246-KMN-N1 Cut Sheet



AutomationDirect VTF series drive output filter, 208-600 VAC, 7-1/2hp at 208/230 VAC, 15hp at 460 VAC and 20hp at 575 VAC, UL Type 1, 3-phase, 25A, output side only. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VTF-246-KMN-N1>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Drive output filter
<b>Series</b>	VTF
<b>Voltage Rating</b>	208-600 VAC
<b>Horsepower by Voltage</b>	7-1/2hp at 208/230 VAC, 15hp at 460 VAC and 20hp at 575 VAC
<b>Enclosure Type</b>	UL Type 1
<b>Number of Phases</b>	3
<b>Amperage Rating</b>	25A
<b>Orientation</b>	Output side only
<b>For Use With</b>	Multiple AC drives

## Agency Approvals

<b>UL Listed File #</b>	E197592
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/VTF-246-KMN-N1.pdf>  
See store item page for other formats.