

VTF-246-RUV-N1 Cut Sheet



AutomationDirect VTF series drive output filter, 208-600 VAC, 30hp at 208 VAC, 40hp at 230 VAC, 75hp at 460 VAC and 100hp at 575 VAC, UL Type 1, 3-phase, 110A, output side only. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/VTF-246-RUV-N1>

Technical Specifications

Brand	AutomationDirect
Item	Drive output filter
Series	VTF
Voltage Rating	208-600 VAC
Horsepower by Voltage	30hp at 208 VAC, 40hp at 230 VAC, 75hp at 460 VAC and 100hp at 575 VAC
Enclosure Type	UL Type 1
Number of Phases	3
Amperage Rating	110A
Orientation	Output side only
For Use With	Multiple AC drives

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/VTF-246-RUV-N1.pdf>
See store item page for other formats.