W143025A250N Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Metal Work pneumatic cylinder, dual guide rod, 25mm bore, 12mm rod diameter, 250mm stroke, double acting, magnetic piston, universal mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/W143025A250N

Technical Specifications

Brand	Metal Work
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	Dual guide rod
Bore Diameter	25mm
Stroke	250mm
Port Size	G1/8 female BSPP
Mounting	Universal

Action Type	Double acting
Magnetic Piston	Yes
Adjustable Cushions	No
Body Material	Aluminum
Rod Material	Chrome-plated steel
Rod Diameter	12mm
Bushing Type	Bronze bushings
Maximum Operating Pressure	145 psi

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/W143025A250N.pdf
See store item page for other formats.