

# W143063A075N Cut Sheet



Metal Work pneumatic cylinder, dual guide rod, 63mm bore, 20mm rod diameter, 75mm stroke, double acting, magnetic piston, universal mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/W143063A075N>

## Technical Specifications

<b>Brand</b>	Metal Work	<b>Mounting</b>	Universal
<b>Item</b>	Cylinder	<b>Action Type</b>	Double acting
<b>Working Fluid</b>	Air or inert gas	<b>Magnetic Piston</b>	Magnetic piston
<b>Cylinder Type</b>	Dual guide rod	<b>Body Material</b>	Aluminum
<b>Bore Diameter</b>	63mm	<b>Rod Material</b>	Chrome-plated steel
<b>Stroke</b>	75mm	<b>Rod Diameter</b>	20mm
<b>Port Size</b>	G1/4 female BSPP	<b>Bushing Type</b>	Bronze bushings

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/W143063A075N.pdf>  
See store item page for other formats.