

# W3604000002 Cut Sheet



Metal Work AND logic element valve, 3-port (3-way), 2-position, double air pilot, 5/32in (4mm) push-to-connect outlet(s), (2) 5/32in (4mm) push-to-connect pilot(s), Cv=0.1.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/W3604000002>

## Technical Specifications

<b>Brand</b>	Metal Work
<b>Item</b>	Valve
<b>Working Fluid</b>	Pneumatic
<b>Valve Type</b>	AND logic element
<b>Port Quantity</b>	3-port (3-way)
<b>Number Of Positions</b>	2
<b>Action</b>	Double air pilot
<b>Body Material</b>	Technopolymer
<b>Body Width</b>	15.9mm

<b>Seal Material</b>	Nitrile
<b>Mounting</b>	DIN rail or panel
<b>Outlet Port</b>	5/32in (4mm) push-to-connect
<b>Pilot Port</b>	(2) 5/32in (4mm) push-to-connect
<b>Flow Coefficient</b>	0.1
<b>Maximum Operating Pressure</b>	116 psi
<b>Minimum Operating Pressure</b>	22 psi
<b>Working Fluid Temperature</b>	14-140 °F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/W3604000002.pdf>  
See store item page for other formats.