

W3604000003 Cut Sheet



Metal Work NOT logic element valve, 3-port (3-way), 2-position, N.O., single air pilot spring return, 5/32in (4mm) push-to-connect inlet(s), 5/32in (4mm) push-to-connect outlet(s), 5/32in (4mm) push-to-connect pilot(s), Cv=0.1.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/W3604000003>

Technical Specifications

Brand	Metal Work
Item	Valve
Working Fluid	Pneumatic
Valve Type	NOT logic element
Port Quantity	3-port (3-way)
Number Of Positions	2
Valve Configuration	N.O.
Action	Single air pilot spring return
Body Material	Technopolymer
Body Width	15.9mm

Seal Material	Nitrile
Mounting	DIN rail or panel
Inlet Port	5/32in (4mm) push-to-connect
Outlet Port	5/32in (4mm) push-to-connect
Pilot Port	5/32in (4mm) push-to-connect
Flow Coefficient	0.1
Maximum Operating Pressure	116 psi
Minimum Operating Pressure	22 psi
Working Fluid Temperature	14-140 °F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/W3604000003.pdf>
See store item page for other formats.