

W797SS1700 Cut Sheet



Wiegmann vortex cooler kit, 1700 BTUH (498W), 25 SCFM (708 SLPM), 120 VAC operating voltage, stainless steel body. For use with NEMA 4 and NEMA 4X enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/W797SS1700>

Technical Specifications

Brand	Wiegmann
Item	Vortex cooler kit
Cooling Capacity	1700 BTUH (498W)
Flow Rating	25 SCFM (708 SLPM)
Operating Voltage	120 VAC
Body Material	Stainless steel
For Use With	NEMA 4 and NEMA 4X enclosures
Kit Includes	Thermostat, solenoid valve, distribution tube and filter

Agency Approvals

UL Listed File #	E32576
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document