

# WA060604GSC Cut Sheet



Wiegmann enclosure, NEMA 3/4, 6 x 6 x 4in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA060604GSC>

## Technical Specifications

|                                     |                     |
|-------------------------------------|---------------------|
| <b>Brand</b>                        | Wiegmann            |
| <b>Item</b>                         | Enclosure           |
| <b>Slope Top</b>                    | No                  |
| <b>NEMA Rating</b>                  | 3/4                 |
| <b>Nominal Enclosure Dimensions</b> | 6 x 6 x 4in (HxWxD) |
| <b>Enclosure Height</b>             | 6.13in              |
| <b>Enclosure Width</b>              | 6.13in              |
| <b>Enclosure Depth</b>              | 4.36in              |
| <b>Mounting</b>                     | Wall                |
| <b>Integral Mounting Feet</b>       | No                  |
| <b>Integral Mounting Flange</b>     | No                  |
| <b>Dual Access</b>                  | No                  |
| <b>Knockouts</b>                    | No                  |
| <b>Material</b>                     | Carbon steel        |
| <b>Color</b>                        | ANSI 61 gray        |
| <b>Finish</b>                       | Powder coat         |
| <b>Cover Type</b>                   | Screw cover         |
| <b>Padlockable</b>                  | No                  |
| <b>Keylocking</b>                   | No                  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E23553                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |