WA060606GSCSS Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Wiegmann enclosure, NEMA 3/4/4X, 6 x 6 x 6in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, screw cover.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/WA060606GSCSS

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Subpanel	No subpanel available for this enclosure
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3/4/4X
Nominal Enclosure Height	6in
Nominal Enclosure Width	6in
Nominal Enclosure Depth	6in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	304 stainless steel
Finish	No. 3 intermediate polished
Cover Type	Screw cover
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E23553
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/WA060606GSCSS.pdf
See store item page for other formats.