

WA060806GSCSS Cut Sheet



Wiegmann enclosure, NEMA 3/4/4X, 6 x 8 x 6in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA060806GSCSS>

Technical Specifications

| | |
|-------------------------------------|---------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 3/4/4X |
| Nominal Enclosure Dimensions | 6 x 8 x 6in (HxWxD) |
| Enclosure Height | 6.13in |
| Enclosure Width | 8.13in |
| Enclosure Depth | 6.32in |
| Mounting | Wall |

| | |
|---------------------------------|-----------------------------|
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | 304 stainless steel |
| Finish | No. 3 intermediate polished |
| Cover Type | Screw cover |
| Shelf | No |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E23553 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WA060806GSCSS.pdf>
See store item page for other formats.