

# WA081004GSCSS Cut Sheet



Wiegmann enclosure, NEMA 3/4/4X, 8 x 10 x 4in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA081004GSCSS>

## Technical Specifications

|                                     |                             |
|-------------------------------------|-----------------------------|
| <b>Brand</b>                        | Wiegmann                    |
| <b>Item</b>                         | Enclosure                   |
| <b>Slope Top</b>                    | No                          |
| <b>NEMA Rating</b>                  | 3/4/4X                      |
| <b>Nominal Enclosure Dimensions</b> | 8 x 10 x 4in (HxWxD)        |
| <b>Enclosure Height</b>             | 8.13in                      |
| <b>Enclosure Width</b>              | 10.13in                     |
| <b>Enclosure Depth</b>              | 4.32in                      |
| <b>Mounting</b>                     | Wall                        |
| <b>Integral Mounting Feet</b>       | No                          |
| <b>Integral Mounting Flange</b>     | No                          |
| <b>Dual Access</b>                  | No                          |
| <b>Knockouts</b>                    | No                          |
| <b>Material</b>                     | 304 stainless steel         |
| <b>Finish</b>                       | No. 3 intermediate polished |
| <b>Cover Type</b>                   | Screw cover                 |
| <b>Padlockable</b>                  | No                          |
| <b>Keylocking</b>                   | No                          |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E23553                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |