

WA100804GIE Cut Sheet



Wiegmann enclosure, NEMA 12/13, 10 x 8 x 4in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA100804GIE>

Technical Specifications

Brand	Wiegmann	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	Carbon steel
Vented	No	Color	ANSI 61 gray
NEMA Rating	12/13	Finish	Powder coat
Nominal Enclosure Dimensions	10 x 8 x 4in (HxWxD)	Cover Type	Hinged screw cover
Enclosure Height	10.31in	Hinge Type	Continuous hinge
Enclosure Width	8.31in	Number of Hinges Per Door	1
Enclosure Depth	4.15in	Shelf	No
Mounting	Wall	Padlockable	No
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E6924
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WA100804GIE.pdf>
See store item page for other formats.