

WA101206GSCG Cut Sheet



Wiegmann enclosure, NEMA 3/4, 10 x 12 x 6in (HxWxD), wall mount, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA101206GSCG>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Slope Top | No |
| NEMA Rating | 3/4 |
| Nominal Enclosure Dimensions | 10 x 12 x 6in (HxWxD) |
| Enclosure Height | 10.13in |
| Enclosure Width | 12.13in |
| Enclosure Depth | 6.40in |
| Mounting | Wall |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Galvanized steel |
| Cover Type | Screw cover |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E23553 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |