

WA121204GSCG Cut Sheet



Wiegmann enclosure, NEMA 3/4, 12 x 12 x 4in (HxWxD), wall mount, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA121204GSCG>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Slope Top	No
NEMA Rating	3/4
Nominal Enclosure Dimensions	12 x 12 x 4in (HxWxD)
Enclosure Height	12.13in
Enclosure Width	12.13in
Enclosure Depth	4.40in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Galvanized steel
Cover Type	Screw cover
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E23553
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document