

# WA202408GSC Cut Sheet



Wiegmann enclosure, NEMA 3/4, 20 x 24 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA202408GSC>

## Technical Specifications

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Brand</b>                        | Wiegmann              |
| <b>Item</b>                         | Enclosure             |
| <b>Slope Top</b>                    | No                    |
| <b>NEMA Rating</b>                  | 3/4                   |
| <b>Nominal Enclosure Dimensions</b> | 20 x 24 x 8in (HxWxD) |
| <b>Enclosure Height</b>             | 20.13in               |
| <b>Enclosure Width</b>              | 24.13in               |
| <b>Enclosure Depth</b>              | 8.36in                |
| <b>Mounting</b>                     | Wall                  |
| <b>Integral Mounting Feet</b>       | No                    |
| <b>Integral Mounting Flange</b>     | No                    |
| <b>Dual Access</b>                  | No                    |
| <b>Knockouts</b>                    | No                    |
| <b>Material</b>                     | Carbon steel          |
| <b>Color</b>                        | ANSI 61 gray          |
| <b>Finish</b>                       | Powder coat           |
| <b>Cover Type</b>                   | Screw cover           |
| <b>Padlockable</b>                  | No                    |
| <b>Keylocking</b>                   | No                    |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E23553                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |