

WA72CPX7312U Cut Sheet



Wiegmann disconnect enclosure, NEMA 12, center post, 72 x 73 x 12in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA72CPX7312U>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Slope Top	No
NEMA Rating	12
Disconnect Mounting	Center post
Nominal Enclosure Height	72.13in
Nominal Enclosure Width	73.75in
Nominal Enclosure Depth	13.36in
Mounting	Floor
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat

Cover Type	2-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Purchase subpanel separately
Requires	Operator adapter plate (sold separately)
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WA72CPX7312U.pdf>
See store item page for other formats.