

WA72X7312U Cut Sheet



Wiegmann disconnect enclosure, NEMA 12, right flange, 72 x 73 x 12in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA72X7312U>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	12
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	72 x 73 x 12in (HxWxD)
Enclosure Height	72.13in
Enclosure Width	73.75in
Enclosure Depth	13.36in
Mounting	Floor
Integral Mounting Feet	No

Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	2-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Purchase subpanel separately
Requires	Operator adapter plate (sold separately)

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WA72X7312U.pdf>
See store item page for other formats.