

# WA72XM6518SSN4 Cut Sheet



Wiegmann disconnect enclosure, NEMA 3R/4/4X/12, right flange, 72 x 65 x 18in (HxWxD), freestanding, 304 stainless steel, No. 3 intermediate polished finish, 2-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA72XM6518SSN4>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Disconnect enclosure
<b>Slope Top</b>	No
<b>NEMA Rating</b>	3R/4/4X/12
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Height</b>	72.13in
<b>Nominal Enclosure Width</b>	66.5in
<b>Nominal Enclosure Depth</b>	19.35in
<b>Mounting</b>	Freestanding
<b>Material</b>	304 stainless steel

<b>Finish</b>	No. 3 intermediate polished
<b>Cover Type</b>	2-door
<b>Hinge Type</b>	Stainless steel continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Latch Type</b>	3-point padlocking handle
<b>Subpanel</b>	Subpanel included
<b>Requires</b>	Operator adapter plate (sold separately)
<b>Additional Information</b>	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

## Agency Approvals

<b>UL Listed File #</b>	E64791
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/WA72XM6518SSN4.pdf>  
See store item page for other formats.