

WA86M4E20 Cut Sheet



Wiegmann enclosure, NEMA 12, 86 x 149 x 20in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 4-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA86M4E20>

Technical Specifications

Brand	Wiegmann	Knockouts	No
Item	Enclosure	Material	Carbon steel
Subpanel	Subpanel included	Color	ANSI 61 gray
Slope Top	No	Finish	Powder coat
NEMA Rating	12	Cover Type	4-door
Nominal Enclosure Height	86in	Hinge Type	Continuous hinge
Nominal Enclosure Width	149in	Number of Hinges Per Door	1
Nominal Enclosure Depth	20in	Latch Type	3-point keylocking/padlocking combo handle
Mounting	Freestanding	Padlockable	Yes
Dual Access	No	Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document